


2D-15 DECOM (4W) RE SS

*Pharma - Wet & Dry Recovery



Characteristics HEPA Included Pharmaceutical Applications AISI 304 & 316 Characteristics Accessories Biohazard Applications Applications Applications Applications Wet & Dry Applications Applications



- HEPA Filter Included with an efficiency of 99.995% on 0.3 micron. Tested: IEST RP-CC001.3. H14 by MPPS method as per EN 1822.
- *Cleanroom compatible. Can be used in the pharmaceutical industry
- For hospital decontamination and recovery of foam
- By-Pass heavy duty motor
- For wet & dry recovery
- All stainless steel AISI 304 construction. High-density polyethylene recovery tank available
- Recovery capacity Disposable Filter Bag (dry) 5 gallons (19 liters),
 Recovery Tank (liquids) 12.5 gallons (47.5 liters)
- · Recovery tank is autoclavable
- Based on a 4-wheel dolly. 4-wheel dolly is autoclavable
- Includes defoaming liquid
- Includes a complete autoclavable tool kit

2D-15 DECOM (4W) RE SS HEPA Shown

All stainless steel AISI 304 construction. Autoclavable recovery tank and dolly. This unit contains a true HEPA Filter (H14) located downstream of the motor housing. This unit has been designed for hospital decontamination and recovery of foam. This unit is cleanroom compatible and can be used in the pharmaceutical industry. Disposable Filter Bags are included for easy and safe disposal of recovered materials. A drain valve is included for emptying the recovery tank. All of our HEPA vacuum cleaners are Aerosol Leak Tested before leaving our facility.NSN: 7910-01-501-9183

U.S. Headquarters

Tiger-Vac Inc. (USA)
73 S.W. 12 Ave. Bldg.1, Unit 7
Dania, FL 33004
USA

Tel.: 954-925-3625 Fax.: 954-925-3626 Web site: http://www.tiger-vac.com Email: sales@tiger-vac.com **International Headquarters**

Tiger-Vac International Inc. 2020 Dagenais Blvd. Laval, Quebec H7L 5W2

Tel.: 450-625-0099 & 450-622-0100 Fax.: 450-625-3388 Web site: http://www.tiger-vac.com Email: support@tiger-vac.com

Specifications for model 2D-15 DECOM (4W) RE SS HEPA

Name	Part Number	Wet Recovery		Vacuum Pressure	Air Flow	Phase	Horse Power	Amperage	Wattage	Hertz	Voltage	Plug Type
2D-15 DECOM (4W) RE SS HEPA	110187A	47.5 L	19 L	2794 mm H ₂ O	212.4 m ³ /h	1	1.6HP	10.5A	1260W	60Hz	120V	120V Plug
	Dimensions: H100.3 cm × W43.2 cm Weight: 29.94 Kg Noise Level: 78.00 dB(A)											
2D-15 HOSPITAL (TC) RE HEPA	110567A	47.5 L	19 L	2794 mm H ₂ O	212.4 m ³ /h	1	1.6HP	10.5A	1207W	60Hz	115V	120V Plug
	Dimensions: H99.1 cm x W66 cm Weight: 29.03 Kg Noise Level: 78.00 dB(A)											

HEPA - High Efficiency Particulate Air Filter

A HEPA filter is a type of air filter, which means it filters the air coming in or out of the vacuum cleaner system. It can remove at least 99.99% of dust, pollen, mould, bacteria and any other airborn particles with a size of 0.3 micron or larger.

North-America: Each HEPA Filter has a minimum filtration efficiency of 99.99% on 0.3 micron. Tested as per IEST-RP-CC001.3.

Europe: Each HEPA Filter has a minimum filtration efficiency of 99.995% on 0.3 micron, rated H14 as per EN 1822 by MPPS method.

Click here to download Tiger-Vac's HEPA Filter's standards chart.

Tools & Accessories

PAPER FILTER BAGS AND ACCESSORIES FOR MODEL 2D-15 DECOM (4W) RE SS HEPA - Included				
Part#	Quantity	Description		
211063	1	PAPER FILTER BAGS (PACKAGE OF 5)		
211282	1	PVC PIPE CONNECTOR FOR PAPER FILTER BAG		
214396	1	BAG ADAPTOR 2"(50mm) -WHITE PVC		

TOOLS AND ACCESSORIES FOR MODEL 2D-15 DECOM (4W) RE SS HEPA - Included					
Part#	Quantity	Description			
323471	1	FOODGRADE HOSE ASSEMBLY 1.25"(32mm)x15'(4.5m) FOR CWR-XX (SMOOTH INSIDE & OUT)			
323330	1	EXTENSION WANDS BOTH STRAIGHT (SET OF 2) Ø1.25"(32mm) -STAINLESS STEEL			
323317	1	UTILITY FLOOR TOOL WITH RUBBER BLADES Ø1.25" (Ø32mm)			
323321	1	ROUND TOOL WITH RUBBER BLADES Ø1.25"(32mm)			
323314	1	UPHOLSTERY FLAT TOOL Ø1.25"(32mm) PVC			
323313	1	CREVICE TOOL Ø1.25"(32mm)x9"(22.9cm) -PVC			
211701	1	DEFOAMING LIQUID (BOTTLE) 909 ml(31 fl oz.)			
381093	1	DRAIN HOSE ASSEMBLY 0.75"(19mm)x5'(1.5m)CLEAR HOSE WITH 0.75"(19mm) STAINLESS STEEL FEMALE CAMLOCK			

TOOLS AND ACCESSORIES FOR MODEL 2D-15 HOSPITAL (TC) RE HEPA - Included					
Part#	Quantity	Description			
381137A	1	PVC CRUSHPROOF SUCTION HOSE ASSEMBLY Ø1.5"(38mm)x10'(3m) FOR Ø1.5"(38mm) SCREW TYPE INTAKE			

TOOLS AND ACCESSORIES FOR MODEL 2D-15 HOSPITAL (TC) RE HEPA - Optional					
Part#	Quantity	Description			
381163	1	WAND ASSEMBLY (2 PCS) Ø1.5"(38mm) -CHROME			
381171	1	UNIVERSAL TOOL INCLUDES RUBBER BLADES & BRUSH STRIPS 18"(45.7cm) -ALUMINUM			
381188	1	CREVICE TOOL SD* 11"(27.9cm) -ALUMINUM			
381111B	1	TOOL KIT# 4B (WITH ALUMINUM CREVICE TOOL)			

Warning:

Do not use this vacuum cleaner to recover explosive dusts or flammable liquids