



Applicable requirements: ANSI/UL 1017 CSA C22.2 No. 243

Characteristics





Pharma

Applications



&



HEPA Included High Efficiency



Cleanroom





Accessories Included

Activated Wet & Dry Carbon Applications

Mercury Recovery

- HEPA Filter Included with an efficiency of 99.995% on 0.3 micron. Tested: IEST RP-CC001.3. H14 by MPPS method as per EN 1822.
- *Cleanroom compatible. Can be used in the pharmaceutical industry
- Designed for mercury recovery
- Pneumatically (air) operated
- Wet & dry recovery
- Available with a high-density polyethylene recovery tank
- EMI/RFI shielded
- Includes a timer (hour counter)
- Includes Mersorb® brand actibated carbon for the adsorption of mercury vapors
- Includes a suction hose, mercury separator and jars with lids
- based on a 4-wheel dolly

High-density polyethylene recovery tank. This unit contains a true HEPA Filter (H14) located upstream of the motor. This unit is designed for mercury recovery and includes a Mersorb® brand activated carbon for the adsorption of mercury vapors. A mercury separator and jars with lids are included. Includes a timer (hour counter). This unit is EMI/RFI shielded. All of our HEPA/ULPA vacuum cleaner are Aerosol Leak Tested before leaving our facility.



Tiger-Vac International Inc. 2020 Dagenais Blvd. Ouest Laval, Quebec H7L 5W2, Canada Tel: 1-800-668-4437 (954-925-3652) Fax: 1-800-668-4439 (954-925-3626) Website: www.tiger-vac.com E-mail: sales@tiger-vac.com

Specifications

| | Unit | MRV-15 AIR (STD) | |
|-----------------------|---------------------|------------------|--|
| Part# | | 110807 | |
| Weight | kg | 39 | |
| Filter Cleaning | | NONE | |
| Dimensions | cm | H117 × W51 × L69 | |
| Wet Recovery | L | 75.7 | |
| Dry Recovery | L | 37.9 | |
| Paper Bag Capacity | L | 18.9 | |
| Vacuum Pressure | mm H ₂ O | 4318 | |
| Air Flow | m³/h | 187 | |
| Venturi | | Single | |
| Minimum Compressor HP | HP | 15 | |
| Air Line Size | | 1/2" | |
| Input Air Volume | m³/h | 76.5 | |
| Input Air Pressure | PSI / Bar | 80 / 5.5 | |
| Airjet | | 6 mm | |

High Efficiency Particulate Air Filter

A HEPA filter is a type of air filter, which means it filters the air coming in or out of the vacuum cleaner system. It can remove at least 99.99% of dust, pollen, mould, bacteria and any other airborn particles with a size of 0.3 micron or larger.

North-America: Each HEPA Filter has a minimum filtration efficiency of 99.99% on 0.3 micron. Tested as per IEST-RP-CC001.3 and OSHA compliant.

Europe: Each HEPA Filter has a minimum filtration efficiency of 99.995% on 0.3 micron, rated H14 as per EN 1822 by MPPS method.

Click here to download Tiger-Vac's HEPA Filter's standards chart.

Ultra Low Penetration Air Filter

A ULPA filter is a type of air filter. It can remove at least 99.999% of dust, pollen, mould, bacteria and any other airborn particles with a size of 0.12 microns or larger.

North-America: Each ULPA Filter has a minimum filtration efficiency of 99.999% on 0.12 micron. Tested as per IEST-RP-CC001.3.

Europe: Each ULPA Filter has a minimum filtration efficiency of 99.9995% on 0.18 micron, rated U15 as per EN 1822 by MPPS method.

EMI Suppresion / RFI Shielding

These cleanroom vacuum cleaners are equipped with an electronic filter suppresser which reduces electromagnetic interference (EMI), both radiated and conducted, below class B limits for digital apparatus as established by the FCC and ISO. It also provides shielding against RFI (Radio Frequency Interference). The electronic filter is wired in line with the motor. If the electronic filter should fail, power to the motor will automatically be cut-off. These vacuum cleaners will not disrupt computers, radio and video monitors and other sensitive electronic equipment.

| HEPA FILTER - Included | | |
|------------------------|-----|-------------------|
| Part# | Qty | Description |
| 211027B | 1 | HEPA FILTER (H14) |

| FILTERS - Included | | |
|--------------------|-----|------------------------------|
| Part# | Qty | Description |
| 211305 | 1 | DOUBLE CLOTH FILTER ASSEMBLY |
| 211394 | 1 | LIQUID FILTER ASSEMBLY |

| ACTIVATED CARBON CARTRIDGE - Included | | |
|---------------------------------------|-----|---|
| Part# | Qty | Description |
| 212200C | 1 | CARBON CARTRIDGE ASSEMBLY WITH 3mm MERSORB (FOR MERCURY VAPORS) |

| ACTIVATED CARBON CARTRIDGES - Optional | | |
|--|-----|---|
| Part# | Qty | Description |
| 212200B | 1 | CARBON CARTRIDGE ASSEMBLY WITH 3mm CARBON (REGULAR) |
| 212200K | 1 | CARBON CARTRIDGE ASSEMBLY WITH 3mm KOGC3/KINA3 CARBON (FOR CHLORIDE VAPORS) |
| 212200L | 1 | CARBON CARTRIDGE ASSEMBLY WITH 3mm A-3 CARBON (FOR ARSINE AND PHOSPHINE VAPORS) |

| MERCURY RECOVERY SEPARATOR AND ACCESSORIES - Included | | | |
|---|-----|---|--|
| Part# | Qty | Description | |
| 212208 | 1 | MERCURY SEPARATOR -STAINLESS STEEL(INCLUDES 2 MERCURY RECOVERY JARS AND (2) LIDS FOR JAR) | |
| 212210 | 1 | JAR FOR MERCURY RECOVERY 20oz(540 ml) WITH LID | |
| 212211 | 1 | CLEAR SUCTION HOSE ASSEMBLY 1"(25.4mm)x8'(2.4m) FOR USE WITH MERCURY SEPARATOR | |

| POLY LINER RECOVERY BAGS - Included | | |
|-------------------------------------|-----|----------------------------|
| Part# | Qty | Description |
| 212368 | 1 | POLY LINERS (PACKAGE OF 5) |

| DISPOSABLE | DISPOSABLE FILTER BAGS AND ACCESSORIES - Included | | | |
|------------|---|--|--|--|
| Part# | Qty | Description | | |
| 211063 | 1 | PAPER FILTER BAGS (PACKAGE OF 5) | | |
| 211845 | 1 | PVC PIPE CONNECTOR FOR PAPER FILTER BAG FOR CWR-15 POLY TANK & MRV-15 (WITH 4 CRIMPS TO FIT ELBOW) | | |

| TOOLS AND ACCESSORIES - Included | | | |
|----------------------------------|-----|--|--|
| Part# | Qty | Description | |
| 212215 | 1 | CLEAR URETHANE SUCTION HOSE ASSEMBLY 10'(3m)WITH 1.5"(38mm) FEMALE CAMLOCK(PVC) ON ONE END | |
| 381092 | 1 | DRAIN HOSE ASSEMBLY 0.75"(19mm)x5'(1.5m)CLEAR HOSE WITH 0.75"(19mm) PVC FEMALE CAMLOCK | |
| 211787 | 1 | AIR SUPPLY HOSE ASSEMBLY STANDARD TYPE Ø0.5"(12.7mm)x50'(15m)W/1 MALE QUICK DISC&1 FEMALE QUICK DISC | |
| 381197 | 1 | CREVICE TOOL 11" (27.9cm) -GREY PVC | |
| 381207 | 1 | REDUCER/ADAPTOR Ø1.5"(38mm) TO Ø1.25"(32mm) -PVC | |
| 323312 | 1 | ROUND BRUSH, Ø1.25"(32mm) | |
| 323314 | 1 | UPHOLSTERY FLAT TOOL, Ø1.25"(32mm), PVC | |
| 381380 | 1 | FLOOR TOOL 14"(35.6cm) ABS WITH NYLON BRUSHES | |
| 381381 | 1 | FLOOR TOOL 14"(35.6cm) WITH SQUEEGEE -ABS | |
| 381382 | 1 | REPLACEMENT SQUEEGEE BLADES (SET) FOR 14"(35.6cm) FLOOR TOOL (ABS & ALUMINUM) | |
| 381351A | 1 | WAND PVC DOUBLE BEND 54"(1.4m) WITH ABS AMERICAN ATTACHMENT | |

WARNINGS:

Do not use these vacuum cleaners to recover explosive dusts or flammable liquids

Tiger-Vac Inc. (USA) 73 S.W. 12 Ave. Bldg. 1, Unit 7 Dania, FL 33004, USA **Tiger-Vac International Inc.** 2020 Dagenais Blvd. Ouest Laval, Quebec H7L 5W2, Canada Tel: 1-800-668-4437 (954-925-3652) Fax: 1-800-668-4439 (954-925-3626) Website: www.tiger-vac.com E-mail: sales@tiger-vac.com